

AMBI-FIT ST-2070LP




LIGHT-POWDERED, LATEX-FREE, INDUSTRIAL GRADE DISPOSABLE NITRILE GLOVES

Shields against chemical splash & industrial hazards. Best for painting, maintenance, automotive & inspections. Ambidextrous design with excellent fit, puncture resistance and grip, with touchscreen compatibility.

FEATURES

- **Lightly Powdered Gloves** provide easy donning with gentle comfort for skin compatibility
- **KYNO Micro-Textured Surface** maintains reliable grip in damp, wet, and variable conditions
- **Flexible Conforming Material** provides a secure, comfortable fit that moves naturally with the hand
- **Liquid-Resistant Design** helps protect against liquid penetration and everyday exposure for dependable task performance
- **Ambidextrous Design** fits either hand, improving efficiency and convenience during frequent changes or bulk use
- **Comfort Moisture Control** reduces dryness and discomfort during extended wear
- **Latex-Free Design** reduces the risk of latex-related allergies
- **Thin Precision Construction** enables accurate handling of small parts and tools

STANDARDS



MATERIALS

Composition: Nitrile
Type: Light-Powdered, Non-Sterile, Silicon-free
Cuff Style: Beaded
Color: Blue
Length: 9.5"

SIZES

7	S
8	M
9	L
10	XL
11	2XL

PACKING DETAILS

100	Glove per Dispenser
1000	Dispenser per Carton

KYNO
TECHNOLOGY



KYNO™ is Stego's single-use glove system designed for skin comfort, dependable protection, and precision performance in demanding work environments

ESSENTIAL TECHNOLOGIES



APPLICATIONS






HAND PROTECTION ENGINEERED. ACHIEVED.

KYNO

TECHNOLOGY

ST-2070LP

AMBI-FIT



Maintains structural integrity against penetration by liquids, aerosols, and fine particulates across full exposure durations.



Designed to accommodate a wide range of hand sizes and shapes through stretch-calibrated material.



Engineered with micro-textured fingertips or palm zones that increase friction surface area.

Textured Fingertips
Promotes Reliable Grip
During Precision Tasks

Smooth Surface
Provides Responsive
Touch For Greater
Dexterity



Maintains high material sensitivity across fingertips and contact zones, allowing precise control.



Formulated with non-irritating compounds and smooth internal surface to reduce friction, chafing, and chemical reactivity.



Optimized glove entry through low-resistance cuff design and internal surface treatment.

Elastic Nitrile
Construction Allows
Freedom Of Movement
And Comfort

Beaded Cuff Helps
Make Donning Easier and
Reduces Cuff Rolling,
Prevents Liquid Run-Off

ENGINEERED WITH STEGO TECHNOLOGIES

PERFORMANCE & COMPLIANCE

ST-2070LP meets the requirements of applicable EN & ANSI/ISEA standards.

EN ISO 21420:2020
+A1:2024



EN ISO 21420:2020 + A1:2024

General Requirements
Dexterity:

5

EN ISO 374-1:2016
+A1:2018



EN ISO 374-1:2016 + A1:2018

Protection Against Dangerous Chemicals

K - Sodium Hydroxide (40%)
P - Hydrogen Peroxide (30%)
T - Formaldehyde (37%)

EN 374-5:2016



EN ISO 374-5:2016

Protection Against Micro-Organisms

EN 388:2016
+A1:2018



EN 388:2016 + A1:2018

Protection Against Mechanical Risks

Abrasion Resistance:
Blade Cut Resistance (Coupe Test):
Tear Resistance:
Puncture Resistance:
Cut Resistance (TDM 100 Test-ISO 13997):

0
0
1
0
X




Suitable for Contact with Foodstuff

EN 455-1



Medical/Food Grade

PACKAGING INFORMATION	7 / S	8 / M	9 / L	10 / XL	11 / 2XL
MASTER CARTON DIMENSION	28.5X24X23 CM	28.5X24X23 CM	28.5X24X23 CM	28.5X24X23 CM	28.5X24X23 CM
NET WEIGHT	3.20 KG	3.60 KG	4.00 KG	4.40 KG	5.50 KG
GROSS WEIGHT	4.00 KG	4.50 KG	5.00 KG	5.50 KG	6.00 KG
CBM	0.016	0.016	0.016	0.016	0.016
HS CODE	39262090	39262090	39262090	39262090	39262090



LIMITATION OF USE

Properly fitting safety gloves are crucial for safety. Poorly-fitting gloves cause irritation and hinder hand movements. Ensure they meet your required safety level and fit comfortably for optimal protection and functionality. The glove should not be worn in areas where there's a risk of entanglement or where there are moving parts. Avoid using gloves if there are signs of damage or defects.